

Feed ejector

SEC-60

Part no.:10.02.01.01079

<https://www.schmalz.com/10.02.01.01079>

Home > Vakuumska tehnologija za automatizaciju > Vacuum Components > Special Grippers > Feed Ejectors > Feed Ejectors SEC > SEC-60

Powerful ejector for very porous parts




Nozzle size: 6 mm

Suction rate (max.): 12,9 m³/h

Material: Aluminum

Design Data



Attribute	Value
D	32 mm
D1	12,50 mm
D2	12,50 mm
G2	M5-F
G3	M3-F
L	14 mm
L1	44 mm
LG3	5 mm
X1	25 mm

Technical Data

Attribute	Value
Max. vacuum	-245 mbar
Suction rate (max.)	215 l/min
Suction rate (max.)	12,90 m³/h
Air consumption suction	140 l/min
Air consumption suction	6,60 m³/h
Pressure range (operating pressure)	2.0 ... 5.0 bar
Operating temperature	°C
Material	Aluminum
Weight	0,04 kg

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Feed ejector

SEC-60

Part no...:10.02.01.01079

<https://www.schmalz.com/10.02.01.01079>

Max. vacuum	-7,23 inHg
Suction rate (max.)	7,59 cfm
Air consumption suction	4,94 cfm
Pressure range (operating pressure)	29.0 ... 72.5
Product family	SEC

Note: Air consumption: At optimal operating pressure (4,5 bar)