

## Flat suction cup (round)

PFG 3.5 SI-CO-55 N003

Part no.:10.01.01.00752

<https://www.schmalz.com/10.01.01.00752>

Home > Vakuumska tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > PFG 3.5 SI-CO-55 N003

### Flat suction cup (round) for smooth or slightly rough surfaces




Size: 3,5

Suction cup material: Silicone SI conductive

Material hardness [Shore A]: 55 Shore A

### Design Data



| Attribute  | Value   |
|------------|---------|
| d          | 2 mm    |
| d1         | 3 mm    |
| Dk         | 4,20 mm |
| Dmax(S)    | 4 mm    |
| Ds         | 3,50 mm |
| H          | 4 mm    |
| H2         | 1,50 mm |
| H3         | 2,50 mm |
| Z (Stroke) | 0,50 mm |

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

### Technical Data

| Attribute                   | Value                  |
|-----------------------------|------------------------|
| Suction force (-600mbar)    | 0,42 N                 |
| Volume                      | 0,02 cm <sup>3</sup>   |
| Curve radius (min) (convex) | 7,50 mm                |
| Size                        | 3,50                   |
| Nipple family               | N 003                  |
| Suction cup material        | Silicone SI conductive |
| Material hardness [Shore A] | 55 Shore A             |

### Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | [info@schmalz.si](mailto:info@schmalz.si)

## Flat suction cup (round)

PFG 3.5 SI-CO-55 N003

Part no...:10.01.01.00752

<https://www.schmalz.com/10.01.01.00752>

Product family

PFG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor  
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

### Accessories



#### SA-NIP N003 M3-AG DN100

Part no...:10.01.01.00316

Thread G1: M3-M

Length L1: 7,5 mm

Fitting length: 2 mm

Material: Aluminum