

Suction plate (round)

SPL-HT 120 FPM-F-65 G1/4-AG

Part no.:10.01.01.13438

<https://www.schmalz.com/10.01.01.13438>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for High-Temperature Applications > Suction Plates for High-Temperature SPL-HT FPM-F > SPL-HT 120 FPM-F-65 G1/4-AG

Suction plate for high-temperature applications



Size: 120


Suction cup material: Fluorocautchuc FPM-F

Material hardness [Shore A]: 65 Shore A

Connection: G1/4-AG

Working temperature max.: 350 °C

Design Data



Attribute	Value
dn	6 mm
Dmax(S)	130 mm
Ds	120 mm
G1	G1/4"-M
H	46 mm
LG1	11 mm
SW1	8 mm
Z (Stroke)	25 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	675 N
Volume	208 cm ³
Curve radius (min) (convex)	300 mm
Size	120
Number of folds	0
Working temperature max.	350 °C
Suction cup material	Fluorocautchuc FPM-F
Weight	295 g

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Suction plate (round)

SPL-HT 120 FPM-F-65 G1/4-AG

Part no.:10.01.01.13438

<https://www.schmalz.com/10.01.01.13438>

Product family

SPL-HT

Spare parts



SPL-HT 120 FPM-F-65

Part no.:10.01.01.13435

Size: 120

Suction cup material: Fluorocautchuc FPM-F

Material hardness [Shore A]: 65 Shore A

Working temperature max.: 350 °C

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de