

Flat suction cup (oval)

SAOF 80x40 NBR-60 G1/4-AG

부품 번호...10.01.05.00314

<https://www.schmalz.com/10.01.05.00314>

홈페이지 > 진공 자동화 기술 > 진공 부품 > 진공패드 > 시트메탈 핸들링용 진공 패드 > Flat Suction Cups SAOF (Oval) > SAOF 80x40 NBR-60 G1/4-AG

Flat suction cup (oval) for very dynamic handling of smooth and oily workpieces



Dimensions (LxB): 80x40


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

Nipple material: Aluminum

Connection: G1/4-AG

디자인 데이터



속성	값
Bmax(S)	43 mm
Bs	38.60 mm
dn	5 mm
G1	G1/4"-M
H	20 mm
LG1	8 mm
Lmax(S)	85 mm
Ls	80.60 mm
SW1	17 mm
Z (Stroke)	4 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

기술 데이터

속성	값
Suction force (-600mbar)	140 N
Lateral force	110 N
Lateral force (oily surface)	100 N
Volume	11.70 cm ³
Curve radius (min) (convex)	50 mm
Hose diameter (rec.) d	4 mm
Number of folds	0

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8462403 |...에서 2
schmalz@schmalz.co.kr

Flat suction cup (oval)

SAOF 80x40 NBR-60 G1/4-AG

부품 번호...10.01.05.00314

<https://www.schmalz.com/10.01.05.00314>

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60 Shore A
Weight	34 g
Product family	SAOF
Dimensions (LxB)	80x40

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m