

Basisejector

SBP HV 2 07 13 S SD

Onderdeelnr...:10.02.01.01731

<https://www.schmalz.com/10.02.01.01731>

Homepage > Vacuümtechniek voor de automatisering > Vacuüm componenten > Vacuümgenerator > Basic ejectoren > Basisuitwerpers SBP-HV/HF > SBP HV 2 07 13 S SD

Basisejector voor universeel gebruik



Shape: High Vacuum

Number of stages: 2

Nozzle diameter: 0,7 mm

Size: 13

Degree of evacuation: 85 %

Pressure optimal: 4 bar


Suction rate (max.): 37,5 l/min

Air consumption suction: 23,5 l/min

Add. function: Silencer

construction shape compact ejectors: With safety valve

Ontwerpgegevens



Attribuut	Waarde
B	23 mm
D	16,50 mm
d2	4,20 mm
G1	G1/8"-F
G2	G1/4"-IG
G3	G1/8"-IG
G5	M4-IG
H	33 mm
H2	8,50 mm
H3	19,50 mm
L	69,50 mm
L1	121 mm
L2	22 mm
L3	25,50 mm
LG3	5,50 mm
X1	14 mm
X2	19 mm
Y1	14 mm

Technische gegevens

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Basisejector

SBP HV 2 07 13 S SD

Onderdeelnr...:10.02.01.01731

<https://www.schmalz.com/10.02.01.01731>

Attribuut	Waarde
Nozzle diameter	0,70 mm
Number of stages	2
Degree of evacuation	85 %
Suction rate (max.)	2,30 m³/h
Suction rate (max.)	37,50 l/min
Air consumption suction	1,45 m³/h
Air consumption suction	23,50 l/min
Sound level free	68 dB(A)
Sound level suction	57 dB(A)
Pressure range (operating pressure)	2,0 ... 6,0 bar
Pressure optimal	4 bar
Recomm. internal hose diameter compressed air	4 mm
Recomm. internal hose diameter vacuum	6 mm
Weight	90,90 g
Operating temperature	0 ... 60 °C
Pressure range (operating pressure)	29,0 ... 87,0
Pressure optimal	58 psi
Suction rate (max.)	1,32 cfm
Air consumption suction	0,83 cfm
Product family	SBP-HV-HF

Accessoires



SET SFE 13

Onderdeelnr...:10.02.01.01579

Width B: 20 mm

Height H: 20 mm

Length L: 27 mm

Construction use: Schmalz Fixation Element

Size: 13

Thread G1: G1/8"-M

Thread G2: M8-AG

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Basisejector

SBP HV 2 07 13 S SD

Onderdeelnr...:10.02.01.01731

<https://www.schmalz.com/10.02.01.01731>



BEF-WIN 36x40x27 5 SFE-13

Onderdeelnr...:10.08.03.00314

Width B: 36 mm

Height H: 40 mm

Length L: 27 mm

Construction use: Schmalz Fixation Element

Size: 13



SEV G1/8-IG G1/4-AG

Onderdeelnr...:10.02.01.01471

External diameter D: 19 mm

Length L: 37 mm

Thread G1: G1/8"-F

Thread G2: G1/4"-AG

Onderdelen



SEP HV 2 07 13 S

Onderdeelnr...:10.02.01.01406

Shape: High Vacuum

Number of stages: 2

Nozzle size: 0,7 mm

Hole diameter: 13 mm

construction shape compact ejectors: With safety valve

Degree of evacuation: 85 %

Pressure range (operating pressure): 2,0 ... 6,0 bar

Pressure optimal: 4 bar

Suction rate (max.): 37,5 l/min

Air consumption suction: 23,5 l/min

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Basisejector

SBP HV 2 07 13 S SD

Onderdeelnr...:10.02.01.01731

<https://www.schmalz.com/10.02.01.01731>



SFE 13 AL

Onderdeelnr...:10.02.01.01419

Hole diameter: 13 mm

Width B: 23 mm

Height H: 33 mm

Length L: 51,5 mm

Thread G1: G1/8"-F

Thread G2: G1/4"-IG

Compressed-air connection: G1/8"-IG

Suction cup connection: G1/4"-IG

Vacuum connection: G1/8"-IG



SHC 2 13

Onderdeelnr...:10.02.01.01496

Number of stages: 2

Hole diameter: 13 mm

External diameter D: 14,2 mm

Length L: 18 mm

Thread G1: M16x1-M



SD 16.5x51.5 SHC 13

Onderdeelnr...:10.02.01.01498

External diameter D: 16,5 mm

Length L: 51,5 mm

Construction use: Schmalz Holder Cap

Size: 13

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl