

Bell suction cup (round)

SAXM 115 ED-85 M14x1.5-AG

Osanro.:10.01.19.00047

<https://www.schmalz.com/10.01.19.00047>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipaineekomponentit > Imukupit > Imukahva metallilevyn käsittelyyn > Bell-Shaped Suction Cups
SAXM > SAXM 115 ED-85 M14x1.5-AG

Bell suction cup (round) for best adaptation to strongly curved surfaces



Size: 115

Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Nipple material: Aluminum

Connection: M14x1.5-AG

Suunnitteludata



Attribuutti	Arvo
dn	6,10 mm
Dmax(S)	129,40 mm
Ds	115,20 mm
G1	M14x1.5-M
H	50,10 mm
LG1	10 mm
SW1	22 mm
Z (Stroke)	20 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	549 N
Lateral force	320 N
Lateral force (oily surface)	584 N
Volume	141,50 cm ³
Curve radius (min) (convex)	50 mm
Hose diameter (rec.) d	6 mm
Size	115

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Bell suction cup (round)

SAXM 115 ED-85 M14x1.5-AG

Osanro.:10.01.19.00047

<https://www.schmalz.com/10.01.19.00047>

Connection	M14x1.5-M
Number of folds	0
Suction cup material	Elastodur ED
Material hardness [Shore A]	85 Shore A
Weight	92,50 g
Product family	SAXM

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Varaosat



SC-A 065 M14x1.5-AG L

Osanro.:10.01.06.02826

Connection geometry: 065

Thread G1: M14x1.5-M

Fitting length: 8 mm

Shape: Self Locking



SAXM 115 ED-85 SC065

Osanro.:10.01.19.00010

Size: 115

Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Bell suction cup (round)

SAXM 115 ED-85 M14x1.5-AG

Osanro.:10.01.19.00047

<https://www.schmalz.com/10.01.19.00047>



SC-S 065 FDC-L

Osanro.:10.01.06.02805

Shape: Frict elem with Self lock