

Basic Ejector

SBP-C 07 S01 NC VS-T

Część nr.:10.02.01.00988

<https://www.schmalz.com/10.02.01.00988>

Strona główna > Technologia podciśnienia w automatyce > Komponenty podciśnieniowe > Generatory podciśnienia > Eżektory podstawowe > Basic Ejectors SBP-C with Additional Functions > SBP-C 07 S01 NC VS-T

Eżektor podstawowy z lekką obudową z tworzywa sztucznego



Nozzle diameter: 0,7 mm

Degree of evacuation: 85 %

Connection: Hose D4(1)-D4(2)

Pressure optimal: 5.4 bar


Suction rate (max.): 16 l/min

Air consumption suction: 24 l/min

Control valve: Normally closed

Function: electronic vacuum switch

Dane projektowe



Atrybut	Wartość
B	10 mm
d	4,20 mm
d1	4 mm
d2	4 mm
D	9 mm
G3	M5-F
H	34 mm
H1	39 mm
H2	5,20 mm
H3	9 mm
H4	17,70 mm
L	78 mm
L1	102 mm
L2	12,50 mm
L3	27 mm
X1	20 mm

Dane techniczne

Atrybut	Wartość
Nozzle diameter	0,70 mm
Degree of evacuation	85 %

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Basic Ejector

SBP-C 07 S01 NC VS-T

Część nr.:10.02.01.00988

<https://www.schmalz.com/10.02.01.00988>

Suction rate (max.)	1 m ³ /h
Suction rate (max.)	16 l/min
Air consumption suction	1,40 m ³ /h
Air consumption suction	24 l/min
Sound level free	65 dB(A)
Sound level suction	59 dB(A)
Pressure range (operating pressure)	3.0 ... 6.0 bar
Pressure optimal	5,40 bar
Recomm. internal hose diameter compressed air	2 mm
Recomm. internal hose diameter vacuum	2 mm
Weight	103 g
Operating temperature	0 ... 50 °C
Pressure range (operating pressure)	43.5 ... 87.0
Pressure optimal	78,30 psi
Suction rate (max.)	0,57 cfm
Air consumption suction	0,85 cfm
Product family	SBP-C

Note: The supply voltage for vacuum switches and solenoid valves is 24 VDC Air consumption: On version with solenoid valves SBP-C 07 (24) / SBP-C 25 (320) and optimal operating pressure Hose diameter: For max. length 2 m

Akcesoria



BEF-PL 110x44.5x3 SBP

Część nr.:10.02.01.00511

Length L: 110 mm

Width B: 44,5 mm

Height H: 3 mm

Construction use: Basic ejector SBP

Basic Ejector

SBP-C 07 S01 NC VS-T

Część nr.:10.02.01.00988

<https://www.schmalz.com/10.02.01.00988>



SET SBP M4-IG

Część nr.:10.02.01.00769

Length L: 50 mm

Width B: 14 mm

Construction use: Basic ejector SBP

Type: M4-IG



ASK B-MIC10 3000 K-2P

Część nr.:21.04.06.00086

Material hose: PUR cable

Electrical connection: Connect. 10mm



ASK B-M8-4 5000 K-4P

Część nr.:10.06.02.00031

Electrical connection: Fem connect M8, 4 pol

Cable length: 5 000 mm

Material hose: PUR cable

Basic Ejector

SBP-C 07 S01 NC VS-T

Część nr.:10.02.01.00988

<https://www.schmalz.com/10.02.01.00988>



VFI CN6/4 50

Część nr.:10.07.01.00241

Connection: Hose 6/4 with Cap nut

Filter pore size: 50 µm



VFI 4/2 50

Część nr.:10.07.01.00329

Connection: Hose 4/2

Filter pore size: 50 µm

Części zamienne



SD M5-AG 9x24

Część nr.:10.02.01.00539

Thread G1: M5-M

External diameter D: 9 mm

Length L: 24 mm

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Basic Ejector

SBP-C 07 S01 NC VS-T

Część nr.:10.02.01.00988

<https://www.schmalz.com/10.02.01.00988>



VS-V-AH-T-PNP M8-4 S

Część nr.:10.06.02.00294

Measuring range: -1,0 ... 0,0 bar

Shape: Horizontal

Switching point adjustment: Teach function

Construction shape vacuum switch: PNP switching

Electrical connection: Male connect M8, 4 pole

Indication: LED

Protection type IP: IP 40

with: fixed hysteresis

Inputs/outputs: 2 digital