

Bell suction cup (round)

SAXM 80 ED-85 G3/8-IG

Część nr.: 10.01.19.00035

<https://www.schmalz.com/10.01.19.00035>

Strona główna > Technologia podciśnienia w automatyce > Komponenty podciśnieniowe > Przyssawki podciśnieniowe > Przyssawki do obsługi blach. > Bell-Shaped Suction Cups SAXM > SAXM 80 ED-85 G3/8-IG

Przyssawka dzwonowa (okrągła)



Size: 80

Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Nipple material: Aluminum

Connection: G3/8-IG

Dane projektowe



Atrybut	Wartość
dn	6,10 mm
Dmax(S)	92,20 mm
Ds	81 mm
G1	G3/8"-F
H	48,30 mm
LG1	12 mm
SW1	22 mm
Z (Stroke)	13,90 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Dane techniczne

Atrybut	Wartość
Suction force (-600mbar)	270 N
Lateral force	150 N
Lateral force (oily surface)	269 N
Volume	51,90 cm ³
Curve radius (min) (convex)	32,50 mm
Hose diameter (rec.) d	6 mm
Size	80

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Bell suction cup (round)

SAXM 80 ED-85 G3/8-IG

Część nr.:10.01.19.00035

<https://www.schmalz.com/10.01.19.00035>

Connection	G3/8"-F
Number of folds	0
Suction cup material	Elastodur ED
Material hardness [Shore A]	85 Shore A
Weight	45 g
Product family	SAXM

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Części zamienne



SC-A 055 G3/8-IG L

Część nr.:10.01.06.02743

Connection geometry: 055

Thread G1: G3/8"-F

Fitting length: 17,2 mm

Shape: Self Locking



SAXM 80 ED-85 SC055

Część nr.:10.01.19.00008

Size: 80

Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Bell suction cup (round)

SAXM 80 ED-85 G3/8-IG

Część nr.:10.01.19.00035

<https://www.schmalz.com/10.01.19.00035>



SC-S 055 FDC-L

Część nr.:10.01.06.02804

Shape: Frict elem with Self lock