

Non-return valve

RSV 18 G1/2-IG MS

Osanro.:10.05.05.00003

<https://www.schmalz.com/10.05.05.00003>

Aloitussivu > Alipainenostimet ja nostinjärjestelmät > VacuMaster-nostolaite > VacuMaster- alipainetarrainten vara- ja kulutusosat VacuMaster > Spare and Wear Parts VacuMaster Window 200/300 > RSV 18 G1/2-IG MS

No-return valve for maintaining the system vacuum in the case of a power failure



Nominal size: 18 mm


Thread G1: G1/2"-F

Nominal flow rate: 26 m³/h

Operating temperature: -20 ... 100 °C

Material: Brass

Suunnitteludata



Attribuutti	Arvo
D	34,50 mm
G1	G1/2"-F
G2	G1/2"-F
L	58,50 mm
SW1	27 mm

Tekniset tiedot

Attribuutti	Arvo
Nominal size	18 mm
Nominal flow rate	26 m³/h
Nominal flow rate	433,10 l/min
Weight	0,19 kg
Product family	RSV