

Bellows suction cup (round)

SAB 125 NBR-60 G1/4-AG

Część nr...10.01.06.00825

<https://www.schmalz.com/10.01.06.00825>

Strona główna > Technologia podciśnienia w automatyce > Komponenty podciśnieniowe > Przyssawki podciśnieniowe > Przyssawki mieszkowe (okrągłe) > Bellows Suction Cups SAB (1.5 Folds) > SAB 125 NBR-60 G1/4-AG

Przyssawka mieszkowa (okrągła) do dynamicznego chwytania gładkich i zaolejonych powierzchni



Size: 125

Suction cup material: Nitrile rubber NBR


Material hardness [Shore A]: 60 Shore A

Nipple material: Aluminum

Connection: G1/4-AG

Number of folds: 1,5

Dane projektowe



Atrybut	Wartość
dn	6 mm
D1	94 mm
Dmax(S)	135 mm
Ds	126 mm
G1	G1/4"-M
H	67,80 mm
LG1	10 mm
SW1	22 mm
Z (Stroke)	32 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Dane techniczne

Atrybut	Wartość
Suction force (-600mbar)	250 N
Pull-off force	558 N
Lateral force	410 N
Lateral force (oily surface)	335 N
Volume	220 cm ³
Curve radius (min) (convex)	140 mm
Hose diameter (rec.) d	9 mm

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Bellows suction cup (round)

SAB 125 NBR-60 G1/4-AG

Część nr.:10.01.06.00825

<https://www.schmalz.com/10.01.06.00825>

Size	125
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60 Shore A
Weight	179,30 g
Product family	SAB
Number of folds	1,50

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m