

Vacuum cup filter

VFT G1/4-IG 100

Part no.:10.07.01.00120

<https://www.schmalz.com/10.07.01.00120>

Home > Vacuum Cup Filters VFT > VFT G1/4-IG 100

Vacuum cup filter with transparent housing and replaceable filter



Connection: G1/4"-F


Shape: Short filter insert

Nominal flow rate: 140 l/min

Nominal flow rate: 8,4 m³/h

Filter pore size: 100 µm

Design Data



Attribute	Value
D	48 mm
G1	G1/4"-F
H	60 mm
H1	50 mm
L	76 mm

Technical Data

Attribute	Value
Connection	G1/4"-F
Nominal flow rate	140 l/min
Nominal flow rate	8,40 m³/h
Max. vacuum	-990 mbar
Overpressure (max) at 25°C	7 bar
Overpressure (max) at 50°C	5 bar
Filter pore size	100 µm
Weight	47 g
Product family	VFT

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Vacuum cup filter

VFT G1/4-IG 100

Part no.:10.07.01.00120

<https://www.schmalz.com/10.07.01.00120>

Spare parts



FILT-EINS 100 25x37 A2 VFT-1/8+1/4

Part no.:10.07.01.00132

Filter pore size: 100 µm

External diameter D: 25 mm

Length L: 37 mm

Filter material: Aust. Stainless steel

Construction use: Filters VFT

Size: 1/8+1/4



HTR-FIL 2S WI VFT1/8-1/2

Part no.:10.07.01.00228

Shape: angled



DR 37-33x3 NBR

Part no.:10.07.01.00154

External diameter D: 37 mm

Length L: 3 mm

Internal diameter d: 33 mm

Material: Nitrile rubber NBR