

Flat suction cup (round)

SAF 40 NBR-45 G3/8-IG

Part no.:10.01.01.11431

<https://www.schmalz.com/10.01.01.11431>

Home > Vakuumska tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Flat Suction Cups SAF > SAF 40 NBR-45 G3/8-IG

Flat suction cup (round) for very dynamic handling of smooth and oily workpieces



Size: 40

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 45 Shore A

Nipple material: Nickel plated

Connection: G3/8-IG

Design Data



Attribute	Value
dn	4 mm
Dmax(S)	46 mm
Ds	41 mm
G1	G3/8"-F
H	38 mm
LG1	9 mm
SW1	22 mm
Z (Stroke)	4 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	69 N
Lateral force	52 N
Lateral force (oily surface)	50 N
Volume	5,30 cm ³
Curve radius (min) (convex)	50 mm
Hose diameter (rec.) d	4 mm
Size	40

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Flat suction cup (round)

SAF 40 NBR-45 G3/8-IG

Part no.:10.01.01.11431

<https://www.schmalz.com/10.01.01.11431>

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	45 Shore A
Weight	44,60 g
Number of folds	0
Product family	SAF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SU 40

Part no.:10.01.01.12856

Size: 40

Clamping range: 35.0 ... 45.0 mm

Temperature resistance: 80 °C