

Bell suction cup (oval)

SAOG 95x40 NBR-45 RA

부품 번호...10.01.01.11669

<https://www.schmalz.com/10.01.01.11669>

홈페이지 > 진공 자동화 기술 > 진공 부품 > 진공패드 > 시트메탈 핸들링용 진공 패드 > Bell-Shaped Suction Cups SAOG (Oval) > SAOG 95x40 NBR-45 RA

Bell suction cup (oval) for very dynamic handling of smooth and oily workpieces



Dimensions (LxB): 95 x 40


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 45 Shore A

Nipple material: Aluminum

Connection: RA

디자인 데이터



속성

값

Bmax(S) 46 mm

Bs 40 mm

dn 4 mm

H 30.50 mm

L4 31.80 mm

Lmax(S) 102 mm

Ls 95 mm

Z (Stroke) 6 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

기술 데이터

속성	값
Suction force (-600mbar)	165 N
Lateral force	97 N
Lateral force (oily surface)	68 N
Volume	26.90 cm ³
Curve radius (min) (convex)	25 mm
Hose diameter (rec.) d	4 mm
Dimensions (LxB)	95 x 40

Schmalz에 문의

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8462403 | ...에서 2
schmalz@schmalz.co.kr

Bell suction cup (oval)

SAOG 95x40 NBR-45 RA

부품 번호...10.01.01.11669

<https://www.schmalz.com/10.01.01.11669>

Suction cup material	Nitrile rubber NBR
Weight	53.90 g
Number of folds	0
Product family	SAOG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m