

Bellows suction cups (round)

FSGA 22 NK-45 G1/8-AG

Part no.:10.01.06.00414

<https://www.schmalz.com/10.01.06.00414>

Home > Vakuumska tehnologija za avtomatizacijo > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups FSGA (1.5 Folds) > FSGA 22 NK-45 G1/8-AG

Bellows suction cup (round) with optimal adaptation to uneven surfaces



Size: 22

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 45 Shore A


Nipple material: Aluminum

Connection: G1/8"-M

Number of folds: 1,5

Vacuum connection: G1/8"-M

Design Data



Attribute	Value
d2	11,70 mm
Dmax(S)	25 mm
dn	3,50 mm
Ds	21,50 mm
G1	G1/8"-M
H	25 mm
LG1	7,50 mm
SW1	14 mm
Z (Stroke)	6 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction cup material	Natural Rubber NK
Material hardness [Shore A]	45 Shore A
Size	22
Number of folds	1,50
Connection	G1/8-AG
Curve radius (min) (convex)	25 mm
Volume	1,40 cm ³

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bellows suction cups (round)

FSGA 22 NK-45 G1/8-AG

Part no.:10.01.06.00414

<https://www.schmalz.com/10.01.06.00414>

Suction force (-600mbar)	5,70 N
Pull-off force	15,20 N
Hose diameter (rec.) d	4 mm
Weight	5,80 g
Product family	FSGA

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N016 G1/8-AG DN350

Part no.:10.01.06.05735

Nipple family: N 016

Thread G1: G1/8"-M

Length L1: 20 mm

Fitting length: 6 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum



FGA 22 NK-45 N016

Part no.:10.01.06.00425

Size: 22

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 45 Shore A

Number of folds: 1,5