

Robots-Set FXCB

ROB-SET FXCB FANUC SPB2

Onderdeelnr...:10.01.43.00148

<https://www.schmalz.com/10.01.43.00148>

Homepage > Vacuümtechniek voor de automatisering > Vacuüm componenten > Vlakke grijpsystemen en eind-effectoren > Vlakke grijpsystemen
FXCB/FMCB > Handling Sets FXCB > ROB-SET FXCB FANUC SPB2

Compleet vacuümsysteem om aan te sluiten op robots met een lichte bouwconstructie




for: FANUC

Type: CRX

Construction shape vacuum switch: NPN switching

Control valve: Normally open

Ontwerpgegevens



Attribuut	Waarde
B	123,20 mm
B1	159 mm
H	158 mm
H1	164 mm
H2	47 mm
L	297 mm
L1	331 mm
L2	114,40 mm
L3	102 mm
dn	10 mm

Technische gegevens

Attribuut	Waarde
Weight	2 kg
Suction rate (max.)	525,90 l/min
Number of suction cells	15
Lift capacity (vertical)	80 N
Max. load (horizontal)	350 N
for	FANUC
Product family	ROB-SET-FXCB

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Robots-Set FXCB


ROB-SET FXCB FANUC SPB2

Onderdeelnr...:10.01.43.00148

<https://www.schmalz.com/10.01.43.00148>

The technical properties of the robot types may vary by region. The stated compatibility of the set is based on standard European models.

Onderdelen



EMVP 2.35 24V-DC 2x3/2 NO/NC CAR

Onderdeelnr...:10.01.11.03420

Length L: 82,1 mm

Width B: 53,7 mm

Height H: 10,8 mm



SD 97x34x20 FXCB

Onderdeelnr...:10.01.43.00005

Length L: 97 mm

Width B: 34 mm

Height H: 20 mm



VSi V D M8-4

Onderdeelnr...:10.06.02.00577

Measuring range: -1,0 ... 0,0 bar

Construction shape vacuum switch: with display

Electrical connection: Stekker M8, 4 pol

Indication: 2xLED

Protection type IP: IP 65

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Robots-Set FXCB

ROB-SET FXCB FANUC SPB2

Onderdeelnr...:10.01.43.00148

<https://www.schmalz.com/10.01.43.00148>



SPB2 40 SI-55 P

Onderdeelnr...:10.01.06.03126

Size: 40

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Number of folds: 2,5

Shape: Push In