

Balg-zuignap (rond)

FSG 7 SI-55 G1/8-IG

Onderdeelnr...:10.01.06.00010

<https://www.schmalz.com/10.01.06.00010>

Homepage > Vacuümtechniek voor de automatisering > Vacuüm componenten > Vacuümzuignappen > Balgzuignappen (rond) > Bellows Suction Cups FSG (2.5 Folds) > FSG 7 SI-55 G1/8-IG

Balg-vacuümgrijper (rond) voor bijzonder oneffen werkstukken



Size: 7

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible


Nipple material: Aluminum

Connection: G1/8"-IG

Number of folds: 2,5

Vacuum connection: G1/8"-IG

Ontwerpgegevens



Attribuut	Waarde
d2	1,80 mm
dn	3,50 mm
Dmax(S)	7 mm
Ds	5,90 mm
G1	G1/8"-F
H	26 mm
LG1	8,50 mm
SW1	14 mm
Z (Stroke)	3 mm

Opmerking: Toelaatbare maattoleranties voor elastomeeronderdelen volgens DIN ISO 3302-1 M3

Technische gegevens

Attribuut	Waarde
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A
Size	7
Number of folds	2,50
Connection	G1/8-IG
Curve radius (min) (convex)	7,50 mm
Volume	0,04 cm ³

Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Balg-zuignap (rond)

FSG 7 SI-55 G1/8-IG

Onderdeelnr...:10.01.06.00010

<https://www.schmalz.com/10.01.06.00010>

Suction force (-600mbar)	0,15 N
Pull-off force	0,90 N
Hose diameter (rec.) d	4 mm
Weight	4,70 g
Product family	FSG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Onderdelen



SA-NIP N016 G1/8-IG DN350

Onderdeelnr...:10.01.06.05731

Nipple family: N 016

Thread G1: G1/8"-F

Length L1: 18,5 mm

Fitting length: 12 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum



FG 7 SI-55 N016

Onderdeelnr...:10.01.06.00055

Size: 7

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

Number of folds: 2,5