

## Spring plunger

FSTA-HD G1/4-AG 25

Część nr.: 10.01.02.00777

<https://www.schmalz.com/10.01.02.00777>

Strona główna > Technologia podciśnienia w automatyce > Komponenty podciśnieniowe > Elementy montażowe > Trzpienie sprężynowe > Tłok sprężynowy FSTA-HD > FSTA-HD G1/4-AG 25

### Króciec sprężysty z górnym i dolnym tłumieniem ""ciężkie zastosowanie""




Suction cup connection: G1/4"-M

Vacuum connection: G1/8"-F

Spring stroke Z: 25 mm

### Dane projektowe



#### Atrybut Wartość

|            |           |
|------------|-----------|
| G1         | G1/8"-F   |
| G2         | G1/4"-M   |
| G3         | M20x1.5-M |
| H          | 114,50 mm |
| H2         | 37,50 mm  |
| LG1        | 12 mm     |
| LG2        | 8,50 mm   |
| LG3        | 40 mm     |
| SW1        | 24 mm     |
| SW2        | 17 mm     |
| SW3        | 17 mm     |
| Z (Stroke) | 25 mm     |

### Dane techniczne

| Atrybut              | Wartość   |
|----------------------|-----------|
| Spring rate          | 0,71 N/mm |
| Spring pretension    | 8,95 N    |
| Spring force, center | 17,80 N   |
| Vertical load        | 2400 N    |
| Horizontal load      | 800 N     |
| Weight               | 185 g     |

### Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | [schmalz@schmalz.pl](mailto:schmalz@schmalz.pl)

## Spring plunger

FSTA-HD G1/4-AG 25

Część nr...:10.01.02.00777

<https://www.schmalz.com/10.01.02.00777>

|                       |             |
|-----------------------|-------------|
| Operating temperature | 0 ... 80 °C |
| Product family        | FSTA-HD     |

Note: Spring force: Referred to 50 % of operating stroke Vertical loading: Maximum static loading Horizontal stress: The specification of the horizontal stress refers to the lower edge of the plunger with extended spring. It is a maximum static stress and it impairs the spring compression and extension in horizontal position

### Akcesoria



#### FLK G1/4-IG G1/4-AG

Część nr...:10.01.03.00178

Thread G1: G1/4"-F

Thread G2: G1/4"-M

Operating temperature: 0 ... 70 °C



#### KGL G1/4-IG G1/4-AG

Część nr...:10.01.03.00110

Thread G1: G1/4"-F

Thread G2: G1/4"-M

Height H: 37,5 mm

## Spring plunger

FSTA-HD G1/4-AG 25

Część nr.:10.01.02.00777

<https://www.schmalz.com/10.01.02.00777>



**KGL G1/4-IG M10x1.25-AG**

Część nr.:10.01.03.00137

Thread G1: G1/4"-F

Thread G2: M10x1.25-M

Height H: 37,5 mm



**FLK G1/4-IG M10x1.25-AG**

Część nr.:10.01.03.00206

Thread G1: G1/4"-F

Thread G2: M10x1.25-M

Operating temperature: 0 ... 70 °C



**HTR-STA 55 1N D20 WI**

Część nr.:10.08.03.00086

Length L: 55 mm

Connection 1: Sliding block

Connection of suction cup, spring plunger: Contour D20-G1/4

Shape: angled

## Spring plunger

FSTA-HD G1/4-AG 25

Część nr.:10.01.02.00777

<https://www.schmalz.com/10.01.02.00777>



### HTR-UNI 2N FSTE-HDB

Część nr.:10.01.03.00332

Operating temperature: °C

Shape: for FSTE-HDB

Cross-beam connection: 2 T-slots



### ST G1/8-AG 4 MS-ROH

Część nr.:10.08.03.00153

Thread G1: G1/8"-M

Hose diameter (rec.) d: 4 mm

Material: Brass

Surface: raw

Length L: 4 mm

Nominal diameter dn: 2,5 mm



### ST G1/8-AG 6 MS-V

Część nr.:10.08.03.00154

Thread G1: G1/8"-M

Hose diameter (rec.) d: 6 mm

Material: Brass

Surface: nickel plated

Length L: 5 mm

Nominal diameter dn: 4,4 mm

## Spring plunger

FSTA-HD G1/4-AG 25

Część nr.:10.01.02.00777

<https://www.schmalz.com/10.01.02.00777>



### ST G1/8-AG 9 MS-V

Część nr.:10.08.03.00155

Thread G1: G1/8"-M

Hose diameter (rec.) d: 9 mm

Material: Brass

Surface: nickel plated

Length L: 5 mm

Nominal diameter dn: 4 mm



### STV-GE G1/8-AG 4

Część nr.:10.08.02.00202

Thread G1: G1/8"-M

Hose diameter: 4 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 7,9 mm

Length L: 13,7 mm



### STV-GE G1/8-AG 6

Część nr.:10.08.02.00204

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 11,4 mm

Length L: 16,4 mm

## Spring plunger

FSTA-HD G1/4-AG 25

Część nr.:10.01.02.00777

<https://www.schmalz.com/10.01.02.00777>



### STV-GE G1/8-AG 8

Część nr.:10.08.02.00206

Thread G1: G1/8"-M

Hose diameter: 8 mm

Material: Brass

Operating temperature: °C

External diameter D: 14 mm

Length L: 20,7 mm



### STV-W G1/8-AG 4

Część nr.:10.08.02.00156

Thread G1: G1/8"-M

Hose diameter: 4 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 16,4 mm



### STV-W G1/8-AG 6

Część nr.:10.08.02.00158

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 20,1 mm

## Spring plunger

FSTA-HD G1/4-AG 25

Część nr.:10.01.02.00777

<https://www.schmalz.com/10.01.02.00777>



### STV-W G1/8-AG 8

Część nr.:10.08.02.00160

Thread G1: G1/8"-M

Hose diameter: 8 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 24 mm



### STV-GE G1/8-AG 6 HT

Część nr.:10.08.02.00389

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 120 °C

External diameter D: 11,6 mm

Length L: 19 mm



### STV-W G1/8-AG 6

Część nr.:10.08.02.00288

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Plastics

Operating temperature: °C

Length L: 20,8 mm

## Spring plunger

FSTA-HD G1/4-AG 25

Część nr...:10.01.02.00777

<https://www.schmalz.com/10.01.02.00777>



### STV-W G1/8-AG 6 HT

Część nr...:10.08.02.00391

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 120 °C

Length L: 22,5 mm



### STV-WF G1/8-AG 4

Część nr...:10.08.02.00166

Thread G1: G1/8"-M

Hose diameter: 4 mm

Material: Nickel plated

Operating temperature: -10 ... 70 °C

Length L: 17,4 mm



### STV-WF G1/8-AG 6

Część nr...:10.08.02.00168

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Nickel plated

Operating temperature: -10 ... 70 °C

Length L: 21,4 mm

## Spring plunger

FSTA-HD G1/4-AG 25

Część nr.:10.01.02.00777

<https://www.schmalz.com/10.01.02.00777>



### STV-WF G1/8-AG 8

Część nr.:10.08.02.00170

Thread G1: G1/8"-M

Hose diameter: 8 mm

Material: Nickel plated

Operating temperature: -10 ... 70 °C

Length L: 23,4 mm



### STV-WF G1/8-AG 10

Część nr.:10.08.02.00257

Thread G1: G1/8"-M

Hose diameter: 10 mm

Material: Nickel plated

Operating temperature: -10 ... 70 °C

Length L: 25,2 mm



### STV-T G1/8-AG 4

Część nr.:10.09.02.00039

Thread G1: G1/8"-M

Hose diameter: 4 mm

Material: Brass

Operating temperature: °C

Length L: 32,5 mm

## Spring plunger

FSTA-HD G1/4-AG 25

Część nr.:10.01.02.00777

<https://www.schmalz.com/10.01.02.00777>



### STV-T G1/8-AG 6

Część nr.:10.09.02.00040

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: °C

Length L: 41,5 mm



### STV-T G1/8-AG 8

Część nr.:10.09.02.00041

Thread G1: G1/8"-M

Hose diameter: 8 mm

Material: Brass

Operating temperature: °C

Length L: 48,7 mm