

Bellows suction cup (round)

SPB4 20 SI-55 G3/8-IG

Part no.:10.01.06.03519

<https://www.schmalz.com/10.01.06.03519>

Home > Vakuum tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Suction Cups for the Packaging Industry > Bellows Suction Cups SPB4 (4.5 Folds) > SPB4 20 SI-55 G3/8-IG

Bellows suction cup (round) for very uneven workpieces



Size: 20


Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Thread G1: G3/8"-F

Number of folds: 4,5

Design Data



Attribute	Value
d2	13,50 mm
dn	11 mm
Dmax(S)	24,40 mm
Ds	21,40 mm
G1	G3/8"-F
H	58,40 mm
LG1	12 mm
SW1	22 mm
Z (Stroke)	10 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	8 N
Pull-off force	11 N
Volume	7,90 cm ³
Hose diameter (rec.) d	9 mm
Number of folds	4,50
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A
Size	20

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bellows suction cup (round)

SPB4 20 SI-55 G3/8-IG

Part no...:10.01.06.03519

<https://www.schmalz.com/10.01.06.03519>

Weight	23 g
Product family	SPB4

Accessories



SIEB 17x0.8 MS-A2 103 0.103/0.07

Part no...:10.07.01.00320

External diameter D: 17 mm

Length L: 0,8 mm

Material: Brass / Stainless steel

Filter pore size: 103 µm



SSB 16-27 ST-VZ

Part no...:10.07.10.00002

Clamping range: 16.0 ... 27.0 mm

Material: Steel

Surface: galvanised



SPI 16 PE SPB4-20

Part no...:10.01.06.02915

Size: 16

Material: Polyethylene

Use: SPB4-20

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bellows suction cup (round)

SPB4 20 SI-55 G3/8-IG

Part no.:10.01.06.03519

<https://www.schmalz.com/10.01.06.03519>

Spare parts



SC 080 G3/8-IG

Part no.:10.01.06.02594

Connection geometry: 080

Vacuum connection: G3/8"-F

Length L1: 32 mm

Fitting length: 17,5 mm

Nominal diameter dn: 11 mm



SPB4 20 SI-55 SC080

Part no.:10.01.06.02588

Size: 20

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Number of folds: 4,5