

Flat suction cup (round)

PFYN 5 NBR-CO-55 M5-IG

Część nr.: 10.01.01.10345

<https://www.schmalz.com/10.01.01.10345>

Strona główna > Technologia podciśnienia w automatyce > Komponenty podciśnieniowe > Przyssawki podciśnieniowe > Przyssawki płaskie (okrągłe)
> Płaskie przyssawki PFYN > PFYN 5 NBR-CO-55 M5-IG

Przyssawka płaska (okrągły)



Size: 5

Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Vacuum connection: M5-F

Dane projektowe



Atrybut	Wartość
dn	1,50 mm
Dmax(S)	5,50 mm
Ds	5 mm
G1	M5-F
H	16,50 mm
LG1	5,50 mm
SW1	8 mm
Z (Stroke)	0,90 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Dane techniczne

Atrybut	Wartość
Suction force (-600mbar)	0,75 N
Volume	0,01 cm ³
Curve radius (min) (convex)	7,50 mm
Hose diameter (rec.) d	2 mm
Size	5
Suction cup material	Nitrile rubber NBR-conductive
Material hardness [Shore A]	55 Shore A

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Flat suction cup (round)

PFYN 5 NBR-CO-55 M5-IG

Część nr...:10.01.01.10345

<https://www.schmalz.com/10.01.01.10345>

Weight 1,40 g

Product family PFYN

Number of folds 0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Części zamienne



SA-NIP N004 M5-IG DN200

Część nr...:10.01.01.03518

Thread G1: M5-F

Length L1: 14 mm

Fitting length: 10 mm

Material: Aluminum



PFG 5 NBR-CO-55 N004

Część nr...:10.01.01.10064

Size: 5

Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A