

Flat suction cup (oval)

SGON 15x5 NBR-55 M5-IG

Część nr...10.01.05.00105

<https://www.schmalz.com/10.01.05.00105>

Strona główna > Technologia podciśnienia w automatyce > Komponenty podciśnieniowe > Przyssawki podciśnieniowe > Przyssawki płaskie (owalne)
> Flat Suction Cups SGON > SGON 15x5 NBR-55 M5-IG

Przyssawka płaska (owalny)



Dimensions (LxB): 15 x 5


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Connection: M5-F

Dane projektowe



Atrybut	Wartość
Bmax(S)	5,50 mm
Bs	5 mm
dn	1,20 mm
G1	M5-F
H	22 mm
LG1	5,50 mm
Lmax(S)	15,50 mm
Ls	15 mm
SW1	8 mm
Z (Stroke)	0,70 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 M3.

Dane techniczne

Atrybut	Wartość
Suction force (-600mbar)	3,10 N
Volume	0,18 cm ³
Curve radius (min) (convex)	4 mm
Hose diameter (rec.) d	2 mm
Dimensions (LxB)	15 x 5
Number of folds	0
Suction cup material	Nitrile rubber NBR

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Flat suction cup (oval)

SGON 15x5 NBR-55 M5-IG

Część nr.:10.01.05.00105

<https://www.schmalz.com/10.01.05.00105>

Material hardness [Shore A] 55 Shore A

Weight 3,50 g

Product family SGON

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Części zamienne



SA-NIP N021 M5-IG DN200

Część nr.:10.01.05.00125

Thread G1: M5-F

Length L1: 15,5 mm

Fitting length: 10 mm

Nominal diameter dn: 2 mm

Material: Aluminum



SGO 15x5 NBR-55 N021

Część nr.:10.01.05.00071

Dimensions (LxB): 15 x 5

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A