

Bellows suction cups (round)

FSGA 78 SI-55 G1/4-AG

Part no.:10.01.06.00094

<https://www.schmalz.com/10.01.06.00094>

Home > Vakuumska tehnologija za avtomatizacijo > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups FSGA (1.5 Folds) > FSGA 78 SI-55 G1/4-AG

Bellows suction cup (round) with optimal adaptation to uneven surfaces



Size: 78

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible


Nipple material: Aluminum

Connection: G1/4"-M

Number of folds: 1,5

Vacuum connection: G1/4"-M

Design Data



Attribute	Value
d2	54 mm
Dmax(S)	84,50 mm
dn	8,20 mm
Ds	74 mm
G1	G1/4"-M
H	53 mm
LG1	11 mm
SW1	21 mm
Z (Stroke)	16 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A
Size	78
Number of folds	1,50
Connection	G1/4-AG
Curve radius (min) (convex)	100 mm
Volume	75,58 cm ³

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bellows suction cups (round)

FSGA 78 SI-55 G1/4-AG

Part no.:10.01.06.00094

<https://www.schmalz.com/10.01.06.00094>

Suction force (-600mbar)	137,40 N
Pull-off force	218 N
Hose diameter (rec.) d	6 mm
Weight	71 g
Product family	FSGA

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N019 G1/4-AG DN820

Part no.:10.01.06.01959

Nipple family: N 019

Thread G1: G1/4"-M

Length L1: 40 mm

Fitting length: 6 mm

Nominal diameter dn: 8,2 mm

Spanner size SW2: 8 mm

Material: Aluminum



FGA 78 SI-55 N019

Part no.:10.01.06.00129

Size: 78

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

Number of folds: 1,5