

Flat suction cup (round)

PFG 6 NBR-CO-55 N004

Part no.:10.01.01.10065

<https://www.schmalz.com/10.01.01.10065>

Home > Vakuumska tehnologija za avtomatizacijo > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > PFG 6 NBR-CO-55 N004

Flat suction cup (round) for smooth or slightly rough surfaces




Size: 6

Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d	4 mm
d1	6 mm
Dk	7,70 mm
Dmax(S)	6,50 mm
Ds	6 mm
H	6,50 mm
H2	2 mm
H3	4 mm
Z (Stroke)	1 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	1,20 N
Volume	0,10 cm ³
Curve radius (min) (convex)	7,50 mm
Size	6
Nipple family	N 004
Suction cup material	Nitrile rubber NBR-conductive
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Flat suction cup (round)

PFG 6 NBR-CO-55 N004

Part no.:10.01.01.10065

<https://www.schmalz.com/10.01.01.10065>

Weight 0,20 g

Product family PFG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SA-NIP N004 G1/8-AG DN200

Part no.:10.01.01.03528

Thread G1: G1/8"-M

Length L1: 17 mm

Fitting length: 5 mm

Material: Aluminum



SA-NIP N004 G1/8-IG DN200

Part no.:10.01.01.03520

Thread G1: G1/8"-F

Length L1: 20 mm

Fitting length: 16 mm

Material: Aluminum

Flat suction cup (round)

PFG 6 NBR-CO-55 N004

Part no.:10.01.01.10065

<https://www.schmalz.com/10.01.01.10065>



SA-NIP N004 M5-AG DN200

Part no.:10.01.01.03526

Thread G1: M5-M

Length L1: 13,5 mm

Fitting length: 5 mm

Material: Aluminum



SA-NIP N004 M5-IG DN200

Part no.:10.01.01.03518

Thread G1: M5-F

Length L1: 14 mm

Fitting length: 10 mm

Material: Aluminum