

Bellows suction cups (round)

FSGA 63 HT1-60 G1/4-IG

Part no.:10.01.06.02477

<https://www.schmalz.com/10.01.06.02477>

Home > Vakuum tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups FSGA (1.5 Folds) > FSGA 63 HT1-60 G1/4-IG

Bellows suction cup (round) with optimal adaptation to uneven surfaces



Size: 63

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A


Nipple material: Aluminum

Connection: G1/4"-F

Number of folds: 1,5

Vacuum connection: G1/4"-F

Design Data



Attribute	Value
d2	44,50 mm
Dmax(S)	68 mm
dn	4,40 mm
Ds	60 mm
G1	G1/4"-F
H	49 mm
LG1	12 mm
SW1	17 mm
Z (Stroke)	15 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A
Size	63
Number of folds	1,50
Connection	G1/4-IG
Curve radius (min) (convex)	100 mm
Volume	43,83 cm ³

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bellows suction cups (round)

FSGA 63 HT1-60 G1/4-IG

Part no.:10.01.06.02477

<https://www.schmalz.com/10.01.06.02477>

Suction force (-600mbar)	85 N
Pull-off force	135 N
Hose diameter (rec.) d	6 mm
Weight	34 g
Product family	FSGA

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N018 G1/4-IG DN440

Part no.:10.01.06.01066

Nipple family: N 018

Thread G1: G1/4"-F


Length L1: 28,8 mm

Fitting length: 15 mm

Nominal diameter dn: 4,4 mm

Spanner size SW2: 5 mm

Material: Aluminum



FGA 63 HT1-60 N018

Part no.:10.01.06.02473

Size: 63

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Number of folds: 1,5